









## VACUUM-HANDY VH

This is a cheap solution to install non porous slabs using vacuum. The vacuum suction force is produced by only pressing the device down onto the surface of the slab. Afterwards the slab can be lifted by hand.

## VACUUM-HANDY VH 1/25

One-man operation for lightweight slabs and short transportation distance

Accurate and quick installation with no gap in-between slabs.

Reduced suitability for two-men operation. ▶ Ergonomically good working position for installation.

To release the slab, just a finger tip is necessary to open a simple valve.

Attention: Can only be used on non porous materials nearby the ground level. Device must never be set down onto edges, as this can damage the seal. Either set it down to an even surface or lay it down sideways for storage.

Also already layed slabs can be picked up again.

Robust seal ring, can be exchanged within seconds without glueing.

 $\triangleright$  By purchasing of an additional two-men handle HG-VH2 the VH 1/25 can be used for two-men operation.

|                      | Suction Plate dimension ${\mathcal O}$ mm (in) | Carrying Capacity kg (Ibs) | Dead Weight kg (Ibs) | Order-Number |  |
|----------------------|--|----------------------------|----------------------|--------------|--|
| VH 1/25 <sup>0</sup> | 280 (11″)                                      | 25 (55)                    | 5 (10)               | 5260.0009    |  |
|                      |  |                            |                      |              |  |

# VACUUM-HANDY VH 2/50

 $\triangleright$  As VH 1/25, but equipped with screw-on type two-men handle instead of the one-men handle.

Especially suitable for more heavy loads and for transportation at longer distances by two men.

| Туре                 | Suction Plate dimension $arnothing$ (mm) | Carrying Capacity (kg) | Dead Weight kg (Ibs) | Order-Number |
|----------------------|--|------------------------|----------------------|--------------|
| VH 2/50 <sup>0</sup> | 280 (11″)                                | 50 (110)               | 8 (18)               | 5260.0010    |
| Accessories          |  |                        |                      |              |

| Туре  | Dead Weight kg (Ibs) | Order-Number |
|---|----------------------|--------------|
| HG-VH2 Two-men handle <sup>0</sup>            | 3 (7)                | 4260.0155    |
| Replacement seal for Type VH 1/25 and VH 2/50 | 4273.0008            |              |
| Replacement seal for Type VH 1/25 and VH 2/50 | )                    |              |

# VACUUM POWER HANDY VPH

Flexible and powerful hand operated laying device for dense products, such as granite or high quality concrete elements up to 150 kg weight.

### **Consisting of the following components:**

Vacuum pump unit with manometer and  $\triangleright$ suction force indicator, battery charging indicator and on/off switch. Complete unit detachable, can also be mounted on other devices.

#### **Special features:**

Special seal, consisting of 2 components for optimised sealing. Even when the suction plate is sitting on sharp edges for a long time, no permanent marks are left in the seal. Therefore no "fold able rests" are necessary to save quard the seal.

Highly wear-resistant seal!

Powered by rechargeable battery 12 V. Special energy saving automatic allows a full day of laying operation without the need of recharging. Handle for 2 men operation, handles Ď height and width adjustable to accomodate with different laying tasks.

- ▶ 1 Suction plate
- ▶ Galvanised

▶ The seal can be exchanged without glue and any tool within 1 minute.

Additionally equipped with lifting eyelet for crane hook (only allowed to work near the ground!).

| Туре   | Carrying Capacity<br>kg (lbs) | Dead Weight<br>kg (lbs) | Suction Plate<br>Dimension mm (in)                        | Order-Number |
|--|-------------------------------|-------------------------|---|--------------|
| VPH 100 •  | 100 (220)*                    | 16 (35)                 | oval 260 x 210 (101/4" x 81/4")                           | 5271.0002    |
| VPH 150 •  | 150 (330)*                    | 16.5 (36)               | oval 440 x 250 (17 <sup>1</sup> /4" x 9 <sup>3</sup> /4") | 5271.0001    |
| SPS 100-26/21 for VPH 100 •                                  |                               |                         |   | 4270.0051    |
| SPS 150-44/25 for VPH 150 •                                  |                               |                         |   | 4270.0050    |
| Spare storage battery for VPH 100 and VPH 150                |                               |                         |   | 2420.0007    |
| Battery charger for VPH 100 and VPH 150                      |                               |                         | 2420.0004   |              |
| Replacement seal for VPH 100                                 |                               |                         | 4273.0004   |              |
| Replacement seal for VPH 150                                 |                               |                         |   | 4273.0012    |
| Accessory: wheel set RS-VPH * Value at 500 mbar low pressure |                               |                         |   |              |

Retrofit with wheel set RS-VPH can be done at any time.

Thus dense slabs can be installed by just one person.

| Туре                | Carrying Capacity kg (Ibs) | Dead Weight kg (lbs) | Order-Number |
|---------------------|----------------------------|----------------------|--------------|
| RS-VPH <sup>●</sup> | 150 (330)                  | 7,6 (20)             | 4271.0072    |

• Durable surface protection by galvanizing

**VACUUM HAND LAYING DEVICES** 

Probst Greiftechnik Verlegesysteme GmbH, Gottlieb-Daimler-Str. 6, 71729 Erdmannhausen, Germany, Tel. +49 7144-3309-0, Fax +49 7144-3309-50, info@probst.eu

Technical data contained in this catalogue can be modified without prior notice in the interest of progress.

012812